

Data Sheet

Item 3019



1. Product description:

Diamond polishing pads with
ULTRAGRIP® backing system

Dimensions (in):	4"
Dimensions (mm):	100
Specification:	HUM - 400 SECO
Grit:	400
Thickness:	3 mm
Max. rpm:	2,000
Line:	Hum °



The diagram shows a large circle with a smaller circle in the center, representing a circular sample with a diameter of 100 mm. The text 'DPUG' is at the top, and '100 mm' is at the bottom.



1. Application

- For dry polishing of granite, marble, and terrazzo surfaces.
- Excellent and consistent finishing results.
- High flexibility.
- The best option when price is the most important factor.

2. Operating instructions

- Dry use only.
- Use with stone polisher model 2561 or variable-speed angle grinder model 2545.
- Mount the pad onto backing pad model 1599 or 1499.
- Install on the machine and let it run free for one minute to verify that it is not damaged.
- Proceed with the polishing operation.
- Apply moderate pressure, as excessive pressure may damage the diamond segments.

3. Safety information

- Always use safety guards.
- Never exceed the maximum operating speed indicated on the label.
- Always wear complete personal protective equipment (gloves, hearing protection, mask, and safety glasses)



Variable Speed Angle Grinder

4. Handling

- Initial inspection must be performed in the original packaging. If there is visible evidence of damage, the product must not be accepted.
- Handle the pads carefully to prevent impacts or drops. If the pad shows cracks, segment detachment, or any visible damage, it must not be mounted.



Variable Speed Angle Grinder

5. Storage

- Pads must be stored in conditions free from moisture, dust, and dirt, preferably in their original packaging, and should not be exposed for long periods to hot, cold, or wet surfaces.

6. Packaging units

- 10 pieces.